



## Magnum Optimum Hopper

Handling and dispensing caps, closures and small items

Strong, versatile and hygienic, the Magnum Optimum Hopper is ideal for safely transporting and dispensing caps, closures, dry food ingredients, pharmaceuticals, etc.


The all-plastic construction combined with smooth sides promotes hygiene and is easy to clean. An optional lid protects contents from rain, dust and other containments.

The hopper includes a funnel-shaped base leading to a wide 350 x 220mm opening for fast emptying. It has a large 958 litre storage capacity and folding sides to save valuable space on return transport.

Strong and tough, the Magnum Optimum Hopper has a 500 Kg carrying capacity and stacks up to five units high; a combined load of over 2 tonnes on the base hopper.

Identification options include drop-in label holders and recessed areas for permanent labelling.

All parts are easily replaced if damaged and the container can be fully recycled at the end of its long service life.



Rental allows you to acquire what you need, when you need it. Logtek's large fleet of trays, bulk boxes, pallets and wheeled dollies ensures our customers meet day to day needs with the flexibility to address peak or seasonal demands.

# Hopper technical specification



## Magnum Optimum Hopper specification

Description:	Hopper c/w two runners, hopper base and folding sides. Suitable for direct food contact.
External dimensions:	1,200 x 1,000 x 1,210 mm 1,180 mm incremental stacked height
Internal dimensions:	1,140 x 940 x 825 mm
Folded height:	505 mm
Volume:	958 litres
Weight:	72.0 Kg
Maximum loading:	500 Kg unit load 2,200 Kg combined load when stacked 1,150 Kg dynamic load (on forklift, etc)

## Operating instructions

Magnum Optimum Hoppers should only be stacked on a flat level surface. Care must be taken to ensure that hoppers are correctly stacked before placing another unit on top.

Hoppers include the following parts:

1. Lid (optional accessory)
2. Foldable sides secured by catches on both short sides
3. Optiframe spacers secure inner funnel base (item 4)
4. Funnel base with 350 x 220mm opening
5. Dispensing slider: pull out to open
6. Pallet base with two outside runners and two feet

Hoppers can be accessed by fork lift vehicle from all four sides. When using pallet 'pump' trucks, care should be taken that the truck wheels are not resting on the runners when raising the unit as this can cause the runners to detach or break.

